



FortiGate® 600D

High Performance Enterprise Firewall for Large Branch Offices



FortiGate 600D

With network bandwidth requirements doubling every 18 months and increases in sophisticated cyber threats, enterprise organizations with large branch offices know they need high-speed network security that also delivers highly effective next generation security.

Superior Next Generation Firewall Performance

The FortiGate 600D appliance delivers superior performance through a combination of purpose-built FortiASIC™ processors, high port density with 10 GE ports and consolidated security features from the FortiOS™ operating system. It delivers better next generation firewall performance compared to alternate products and provides the best price/performance in the industry.

Deeper Visibility and Top-rated Security

This breakthrough threat prevention performance allows organizations to run NSS Labs Recommended intrusion prevention and application control and VB100 certified antimalware capabilities for deeper inspection. Rich console views and reports together with a flexible policy engine provide the visibility and control to empower employees yet secure your enterprise.

Finally, these features of the FortiGate FortiOS Network Security Platform are routinely validated by independent real-world tests and are consistently getting superior ratings in security effectiveness.

Highlights

Firewall Performance	IPS Performance	Interfaces
36 Gbps	7 Gbps	Multiple 10 GE SFP+, GE SFP and GE RJ45


Features & Benefits

- Superior hardware accelerated next generation firewall offers best-in-class price/performance ratio
- Integrated high port density delivers maximum flexibility and scalability
- NSS Labs Recommended NGFW and NGIPS with consolidated security delivers top-rated protection
- Application control plus identity and device-based policy enforcement provides more granular protection
- Intuitive management interface enables broad and deep visibility that scales from a single FortiGate to thousands



HARDWARE

FortiGate 600D



Interfaces

- | | |
|--|--|
| <ul style="list-style-type: none"> 1. Console Port 2. 2x USB Ports 3. 2x GE RJ45 Management Ports 4. 8x GE SFP Slots | <ul style="list-style-type: none"> 5. 8x GE RJ45 Ports 6. 2x 10 GE SFP+ Slots 7. FRPS Connector |
|--|--|



Powered by FortiASICs

- Custom FortiASIC™ processors deliver the power you need to detect malicious content at multi-Gigabit speeds
- Other security technologies cannot protect against today's wide range of content and connection-based threats because they rely on general-purpose CPUs, causing a dangerous performance gap
- FortiASIC processors provide the performance needed to block emerging threats, meet rigorous third-party certifications, and ensure that your network security solution does not become a network bottleneck

Network Processor

Fortinet's new, breakthrough FortiASIC NP6 network processor works inline with FortiOS functions delivering:

- Superior firewall performance for IPv4/IPv6, SCTP and multicast traffic with ultra-low latency down to 3 microseconds
- VPN, CAPWAP and IP tunnel acceleration
- Anomaly-based intrusion prevention, checksum offload and packet defragmentation
- Traffic shaping and priority queuing

Content Processor

The FortiASIC CP8 content processor works outside of the direct flow of traffic, providing high-speed cryptography and content inspection services including:

- Signature-based content inspection acceleration
- Encryption and decryption offloading

10 GE Connectivity

High speed connectivity is essential for network security segmentation. The FortiGate 600D provides 10 GE slots that simplify network designs without relying on additional devices to bridge desired connectivity.

SOFTWARE



FortiOS Management UI –
FortiView, Policy Table and Application Control Panel

FortiOS

Control all the security and networking capabilities across the entire FortiGate platform with one intuitive operating system. Reduce operating expenses and save time with a truly consolidated next generation security platform.

- A truly consolidated platform with one OS for all security and networking services for all FortiGate platforms.
- Industry-leading protection: NSS Labs Recommended, VB100, AV Comparatives and ICSA validated security and performance.
- Control thousands of applications, block the latest exploits, and filter web traffic based on millions of real-time URL ratings.
- Detect, contain and block advanced attacks automatically in minutes with integrated advanced threat protection framework.
- Solve your networking needs with extensive routing, switching, WiFi, LAN and WAN capabilities.
- Activate all the ASIC-boosted capabilities you need on the fastest firewall platform available.



For more information, please refer to the FortiOS data sheet available at www.fortinet.com

SERVICES

FortiGuard™ Security Services

FortiGuard Labs offers real-time intelligence on the threat landscape, delivering comprehensive security updates across the full range of Fortinet's solutions. Comprised of security threat researchers, engineers, and forensic specialists, the team collaborates with the world's leading threat monitoring organizations, other network and security vendors, as well as law enforcement agencies:

- **Real-time Updates** — 24x7x365 Global Operations research security intelligence, distributed via Fortinet Distributed Network to all Fortinet platforms.
- **Security Research** — FortiGuard Labs have discovered over 170 unique zero-day vulnerabilities to date, totaling millions of automated signature updates monthly.
- **Validated Security Intelligence** — Based on FortiGuard intelligence, Fortinet's network security platform is tested and validated by the world's leading third-party testing labs and customers globally.



For more information, please refer to <http://forti.net/guard>

FortiCare™ Support Services

Our FortiCare customer support team provides global technical support for all Fortinet products. With support staff in the Americas, Europe, Middle East and Asia, FortiCare offers services to meet the needs of enterprises of all sizes:

- **Enhanced Support** — For customers who need support during local business hours only.
- **Comprehensive Support** — For customers who need around-the-clock mission critical support, including advanced exchange hardware replacement.
- **Premium Services** — For global or regional customers who need an assigned Technical Account Manager, enhanced service level agreements, extended software support, priority escalation, on-site visits and more.
- **Professional Services** — For customers with more complex security implementations that require architecture and design services, implementation and deployment services, operational services and more.



For more information, please refer to <http://forti.net/care>

SPECIFICATIONS

FORTIGATE 600D	
Interfaces and Modules	
Hardware Accelerated 10 GE SFP+ Slots	2
Hardware Accelerated GE SFP Slots	8
Hardware Accelerated GE RJ45 Ports	8
GE RJ45 Management	2
USB Ports (Client / Server)	1 / 2
Console Port	1
Onboard Storage	120 GB
Included Transceivers	2 SFP SX
System Performance and Capacity	
IPv4 Firewall Throughput (1518 / 512 / 64 byte, UDP)	36 / 36 / 24 Gbps
IPv6 Firewall Throughput (1518 / 512 / 86 byte, UDP)	36 / 36 / 24 Gbps
Firewall Latency (64 byte, UDP)	3 µs
Firewall Throughput (Packet per Second)	36 Mpps
Concurrent Sessions (TCP)	5.5 Million
New Sessions/Second (TCP)	270,000
Firewall Policies	10,000
IPsec VPN Throughput (512 byte)	20 Gbps
Gateway-to-Gateway IPsec VPN Tunnels	2,000
Client-to-Gateway IPsec VPN Tunnels	10,000
SSL-VPN Throughput	2.2 Gbps
Concurrent SSL-VPN Users (Recommended Maximum)	5,000
IPS Throughput (HTTP / Enterprise Mix)	7 / 4 Gbps
SSL Inspection Throughput	3.5 Gbps
NGFW Throughput	2.4 Gbps
CAPWAP Throughput	10 Gbps
Virtual Domains (Default / Maximum)	10 / 10
Maximum Number of FortiAPs (Total / Tunnel)	1024 / 512
Maximum Number of FortiTokens	1,000
Maximum Number of Registered Endpoints	2,000
High Availability Configurations	Active-Active, Active-Passive, Clustering

FORTIGATE 600D	
Dimensions and Power	
Height x Width x Length (inches)	1.73 x 17 x 12.68
Height x Width x Length (mm)	44 x 432 x 322
Weight	11.46 lbs (5.2 kg)
Form Factor	1 RU
AC Power Supply	100–240V AC, 60–50 Hz
Power Consumption (Average / Maximum)	191 W / 126 W
Current (Maximum)	110V/4A, 220V/2A
Heat Dissipation	650 BTU/h
Redundant Power Supplies	Supports FRPS-100
Operating Environment and Certifications	
Operating Temperature	32–104°F (0–40°C)
Storage Temperature	-31–158°F (-35–70°C)
Humidity	10–90% non-condensing
Operating Altitude	Up to 9,843 ft (3,000 m)
Compliance	FCC Part 15 Class A, C-Tick, VCCI, CE, UL/cUL, CB
Certifications	ICSA Labs: Firewall, IPsec, IPS, Antivirus, SSL-VPN

Note: All performance values are "up to" and vary depending on system configuration. IPsec VPN performance is based on 512 byte UDP packets using AES-256+SHA1. NGFW performance is measured with Flow AV (Quick Mode), IPS and Application Control enabled, based on Enterprise Traffic Mix. SSL Inspection is measured with IPS enabled and HTTP traffic, using TLS v1.2 with AES256-SHA. CAPWAP performance is based on 1444 byte UDP packets.

For complete, up-to-date and detailed feature set, please refer to the Administration Handbook and FortiOS Datasheet.

ORDER INFORMATION

Product	SKU	Description
FortiGate 600D	FG-600D	2x 10 GE SFP+ slots, 10x GE RJ45 ports, 8x GE SFP slots, FortiASIC NP6 and CP8 hardware accelerated, 120 GB onboard SSD storage.
Optional Accessories/Spares		
1 GE SFP LX Transceiver Module	FG-TRAN-LX	1 GE SFP LX transceiver module for all systems with SFP and SFP/SFP+ slots
1 GE SFP RJ45 Transceiver Module	FG-TRAN-GC	1 GE SFP RJ45 transceiver module for all systems with SFP and SFP/SFP+ slots
1 GE SFP SX Transceiver Module	FG-TRAN-SX	1 GE SFP SX transceiver module for all systems with SFP and SFP/SFP+ slots
10 GE SFP+ Transceiver Module, Short Range	FG-TRAN-SFP+SR	10 GE SFP+ transceiver module, long range for all systems with SFP+ and SFP/SFP+ slots
10 GE SFP+ Transceiver Module, Long Range	FG-TRAN-SFP+LR	10 GE SFP+ transceiver module, long range for all systems with SFP+ and SFP/SFP+ slots
10 GE SFP+ Active Direct Attach Cable, 10m / 32.8 ft	SP-CABLE-ADASFP+	10 GE SFP+ active direct attach cable, 10m / 32.8 ft for all systems with SFP+ and SFP/SFP+ slots
External Redundant AC Power Supply	FRPS-100	External redundant AC power supply for up to 4 units: FG-300C, FG-310B, FS-348B and FS-448B. Up to 2 units: FG-200B, FG-200D, FG-240D and FG-300D, FG-400D, FG-500D, FG-600D, FHV-500D, FDD-200B, FDD-400B, FDD-600B and FDD-800B



GLOBAL HEADQUARTERS
Fortinet Inc.
899 Kifer Road
Sunnyvale, CA 94086
United States
Tel: +1.408.235.7700
www.fortinet.com/sales

EMEA SALES OFFICE
905 rue Albert Einstein
Valbonne 06560
Alpes-Maritimes, France
Tel: +33.4.8987.0500

APAC SALES OFFICE
300 Beach Road 20-01
The Concourse
Singapore 199555
Tel: +65.6395.2788

LATIN AMERICA SALES OFFICE
Sawgrass Lakes Center
13450 W. Sunrise Blvd., Suite 430
Sunrise, FL 33323
United States
Tel: +1.954.368.9990